

*Turbidity Checker* **NEW**

# TSC-10(E)

## Make a new style of Turbidity Measurement

Easy Installation, Simple Operation.



### 90 degree scattered light method

Turbidity Checker TSC-10(E) uses a method of 90 degree scattered light as the measuring principle of the world common standard.



### Sapphire glass of the optical windows

The optical windows are made of hard-to-scratch sapphire glass. It enables to scrub the window surface to maintain the Turbidity Checker.



### Built-in wiper cleaning system

The Built-in wiper cleaning system certainly keeps lenses clean.



### Compact design

The compact design makes it possible to install easily.

